Multi-Bore Polyurethane

Specifications

Temperature Range -40°F to +125°F

Vacuum Rating
To 28" Hg.

Diameter Tolerances ±.005"

Tube Markings

None

Working Pressure 3:1 Safety Factor

UV Stabilized

85A

Resin Compliance
See Fre-Thane®
compliances on page 8

Suggested Fittings
Barb


Standard Tail Lengths 8" and 16"



Multi-Bore Polyurethane

ulti-Bore tubing is produced using our Fre-Thane® polyurethane in a single extrusion. Unlike MCR, it is made in one extrusion, which means the tube can only be made in a single color. Unlike MCR, Multi-Bore can't be separated cleanly and should not be used with push-in fittings.

If you require more colors than are listed here, consider using our Multi-Colored Ribbon (MCR).



85A Multi-Bore Polyurethane

Part Number & Packaging Color Code Unit Size	OD	ID	Configuration	Standard Colors	Working Pressure 75°F/25°C 150°F/65°C	lbs./ 100'	Fitting
3J-028 100' Bag 3A-028 1000' Reel	1/8"	.066"	Triple Tube	10 14	125 PSI 50 PSI	1.7	В
4J-026 100' Bag 4A-026 500' Reel	1/8"	.066"	Quad Tube	10	125 PSI 50 PSI	2.2	В
2J-016 100' Bag 2A-016 500' Reel	1/4"	1/8"	Twin Tube	0 05 10 27	150 PSI 60 PSI	4.1	В
4J-023 50' Bag 4A-023 250' Reel	1/4"	1/8"	Quad Tube	(i)	150 PSI 60 PSI	8.4	В

90A Multi-Bore Polyurethane

Part Number & Packaging Color Code Unit Size	OD	ID	Configuration	Standard Colors	Working Pressure 75°F/25°C 150°F/65°C	lbs./ 100'	Fitting
2J-006 100' Bag 2B-006 1000' Reel 2A-006 2000' Reel	1/8"	1/16"	Twin Tube	0) 10 14	190 PSI 75 PSI	1.1	В
2J-013 100' Bag 2A-013 500' Reel	1/4"	.159"	Twin Tube	14	130 PSI 50 PSI	2.9	В
Variations Available: Coiling • Cutting • Bonding • Printing • Packaging • S						• Sizes	

Fre-Thane® Multi-Bore Polyurethane Coils

Part Number & Color Code	OD	ID	Bore/ DUR	Standard Colors		Pressure 150°F/65°C	Material Length	Working Length	Retracted Length	Coil ID
2V-006	1/8"	1/16"	Twin 90A	0) 10 14	160 PSI	65 PSI	<i>7</i> '	5'	6"	3/4"
2W-016	1/4"	1/8"	Twin 85A	0 0502	130 PSI	50 PSI	10'	8'	12.5"	1"
4W-023	1/4"	1/8"	Quad 85A	10	130 PSI	50 PSI	10'	7'	21"	1-1/4"
Variations	Variations Available:						Cuttir	ng • Print	ting • Pac	kaging

Resource Guide-Chemical Resistance Chart

his information was provided to Freelin-Wade by our suppliers and other sources. It is to be used only as a general reference guide to aid in the selection of products in which chemical and material compatibility issues are a factor. This guide is not intended as a complete nor conclusive database. Freelin-Wade does not guarantee these ratings since the resistance of a material can be greatly affected by the temperature, consistency, and presence of other chemicals. Ultimately, the consumer must determine the chemical compatibility of an item based on the conditions in which the product is being used.

	PUR	PE	PVC	Nylon	Kynar
Acetic Acid, Glacial Acetic Acid, 30%	4	2	4	2	1
Acetone	4	2	4	1	4
Acetylene Alkazene	4	•	1	1	-
Aluminum Chloride (aq) Aluminum Nitrate (aq)	3	2	1 2		1
Ammonia Anhydrous	4	2	1	i	4
Ammonia Gas (cold) Ammonia Gas (hot) Ammonium Chloride (aq) 40%	4		-	1	4
Ammonium Chloride (aq) 40% Ammonium Sulfate (aq)	2	1	1	1	1
Amyl Alcohol Amyl Naphthalene	4	2	1		1
Animal Fats	1	-	-		-
Aqua Regia Arsenic Acid	3	2	3		1
Asphalt ASTM Fuel A	2	1	1		1
ASTM Fuel B	3	-	. 4		-
ASTM Fuel C Barium Chloride (aq)	3 1	1	1	1	1
Beer Beet Sugar Liquors	2	2	1	1	1
Benzene	3	4	3	1	1
Benzine Blast Furnace Gas	2	-	-	-	
Bleach Solutions Borax	4	1	1		1
Boric Acid	1	1	i	-	1
Brake Fluid Brine	2	•	3	•	1
Bromine Water	4 2	-	3	4	1
Bunker Oil Butane	1	3	3	1	1
Butter Butyl Alcohol (Butanol)	3	1	3	1	1
Butylene Calcium Chloride (aq)	4	1	1	i	1
Calcium Hydroxide (aq)	2	i	2		1
Calcium Nitrate (aq) Calcium Sulfide (aq)	1	-	1	1	1
Cane Sugar Liquors	4	- 4	1	-	1
Carbolic Acid Carbon Dioxide	1	2	1	-	1
Carbonic Acid Carbon Monoxide	4	2	1	-	1
Carbon Tetrachloride Castor Oil	4	4	4	3	1
Chlorine (dry) Chlorine (wet)	4	3	4	4	1
Chlorine (wet) Chloroform	4	3	4	3	1
Chlorox	4	ī	4	4	1
Chromic Acid 50%	1	i	2	1	1
Coal Tar (Creosote) Coconut Oil	3	i .	1	-	1
	1	1	1		-
Copper Chloride (aq)	1	2	1		1
Coke Oven Gas Copper Chloride (aq) Copper Cyanide (aq) Corn Oil	1	2	1 2		1
Coffon Seed Oil	1	1	2	4	1
Creosol (Methyl Phenol) Cychlohexane	1	4	4	1	i
Denatured Alcohol Detergent Solution	3	1	1		
Diesel Oil	2	3	1		4
Dioxane Dowtherm Oil	3	-	-	- :	-
Dry Cleaning Fluids Ethane	4	-	1	-	-
Ethyl Acrylate	4	- 2	- 3	3	1
Ethyl Alcohol (Ethanol) Ethyl Benzine	4	-	-	-	-
Ethyl Cellulose Ethyl Chloride	2	4	4		1
Ethyl Ether	3	4	4	-	1
Ethylene Chloride Ethylene Glycol ⁵ (Anti-Freeze)	4	4 1	4 1	1	1
Ethylene Oxide Ethylene Trichloride Ferric Chloride (aq) Ferric Sulfate (aq) Ferric Sulfate (aq)	4	3	3	1	1
Ferric Chloride (aq)	1	2	1		1
Ferric Sulfate (aq)	1 2	- 1	1		1
Fluroine (Liquid) Formaldehyde (RT)	4	3	4	1	1
Formic Acid Freon 11	4	2	į	4	1
Freon 12	4 1	3 1	1	1	-
Freon 22 Fuel Oil (Bunker 'C')	4 2	3	1	1	1
Gasoline (100 Octane, High Test)	3	4	3	1	1
Glue Glycerin (Glycerol)	1	1	3 1	1	1
Glycerin (Glycerol) Glycols Green Sulfate Liquor	4	-	-	1 -	-
Hexane	2	41	2 ²	-	ī
Hydraulic Oil Hydrochloric Acid (cold) 37%	1	1-3 2	1 2	4	1
Hydrochloric Acid (hot) 37%	4	-	-	4	1
Hydrofluroic Acid (Conc.) (cold) Hydrofluroic Acid (Conc.) (hot)	4	2	-	•	1
Hydrogen Gas Isobutyl Alcohol	3	1	1 -	1	1
Isooctane	3 2 4	3	1		1
Isopropyl Acetate Isopropyl Alcohol (Isopropanol)	3	1	-	1	1
Isopropyl Ether Kerosene	2 1	1 4	2	1	1
	·		_	·	

	PUR	PE	PVC	Nylon	Kynar
Lacquers Lacquer Solvents	4	1	4		
Lard	1	i	i		1
Lavender Oil Lead Acetate (aq)	4	1	1		1
Linseed Oil Liquified Petroleum Gas	2	3	1	1	1
Lubricating Oils	1-2 ³	4	2	1	1
Lye Magnesium Chloride (aq)	4	1-4 ⁴	1-2	1	1
Magnesium Hydroxide (aq)	4	2	1	-	1
Mercury Methane	3	1	1 2	1	1
Methyl Acetate	4	2	4	1	1
Methyl Acrylate Methyl Alcohol (Methanol)	4	1	1	i	i
Methyl Butyl Ketone Methyl Chloride	4	4	1	1	1
Methylene Chloride Methyl Ethyl Ketone	4	4	4	-	1
Methyl Ethyl Ketone Methyl Isobutyl Ketone	4	2	4	1	4
Milk	4	- 1	- 1	1	1
Mineral Oil Motor Oil 20W, 10W40	1	3	1	1	1
Naphtha (Lighter Fluid)	2	4	1	1	1
Naphthalene (Moth Repellent) Natural Gas	2	2	4 1	1	1
Neatsfoot Oil Nitric Acid 70%	1	-	-	- 4	1
Nitric Acid (Dilute) 10%	3	2	1	4	1
Nitroethane	4	i	-		1
N-Octane Oleic Acid	2	1	3	1	1
Oleic Acid Oleum Spirits Olive Oil	3 1	4	4		4 1
Oxygen (cold)	1	-	-	1	1
Oxygen (cold) Oxygen (200-400F)	4		-		
Paint Thinner, Duco Perchloric Acid	4	ī	3	-	1
Perchloroethylene	2	3	3	3	1
Petroleum - Below 250F Petroleum - Above 250F	4	-	-	4	-
Phenol (Carbolic Acid) Phenyl Ethyl Ether Phosphoric Acid - 45%	3	2	3-4	4	1
Phosphoric Acid - 45%	4	1	2	2	1
Pickling Solution Picric Acid	4	1	4	3	1
Potassium Acetate (aq)	4	-	-	-	1
Potassium Chloride (aq) Potassium Cyanide (aq)	1	2	1		1
Potassium Hydroxide (aq)	4	1	1	3	4
Producer Gas Propane	1	1	1	1	1
Propyl Alcohol (Propanol)	4	ī	1	-	1
Propylene Propylene Glycol (Anti-Freeze)	3	1	3	2	1
Propylene Oxide	4	2	-	-	4
Pydraul, 10E, 29 ELT Pydraul 30E, 50E, 65E	4		-		
Pydraul, 115E	4	-		- :	
Pydraul 230E, 312C, 540C Rapeseed Oil	2	4	-	-	-
RJ-1 (MIL-F-23338 B) RP-1 (MIL-F-25576 C)	1				
Salt Water	2	1	1	1	1
Sewage Silicate Esters	1	-	-	-	1
Silicone Oils	1	1	i	•	1
Silver Nitrate Skydrol 500	1	1	1		1
Skydrol 500 Skydrol 700	4	-	-	-	
Soap Solutions Sodium Chloride (aq)	3	4	1	1	-
Sodium Hydroxide (aq)	4	1	1	2	4
Sodium Peroxide (aq) Sodium Phosphate (aq)	1	1 -	2		1
Sodium Sulfate (aq)	1	1	1		-
Soy Bean Oil Stoddard Solvent	2 1	3	1		1
Styrene (Monomer)	4	2	4	- 1	1
Sucrose Solution Sulfuric Acid (Dilute Battery Acid)	3	1	i	-	i
Sulfuric Acid (Conc) Sulfuric Acid (20% Oleum)	4	2	4		1
Sulturous Acid	4	2	1	- :	-
Tannic Acid Tetrochlorethylene	4	1 2	1		1
Toluene (Toluol)	4	3	4	1	1
Transformer Oil Transmission Fluid Type A	2		2	-	
Trichloroethane	4	4	3	3	1
Trichloroethylene Turbine Oil	4 1	3	4	3 1	1
Turpentine	4	4	4	1	1
Varnish Vinegar	3	3	4	1	1
Vinyl Chloride	4	4	4	-	1
Water Whiskey, Wines	1 2	1	1	1	1
White Oil	1	-	-	-	-
Wood Oil Xylene	3	4	4	1	1
Zinc Acetate (aq)	4	-			i
Zinc Chloride (aq)	2	1	T		1
1 Petroleum Base 2 Synthetic	Base =	1. Petr	oleum	Base :	= 3

Rating Scale

- 1= Little or no impact
- 2= Minor effect
- 3= Moderate effect
- 4= Severe effect

1 Petroleum Base **2** Synthetic Base = 1, Petroleum Base = 3 **3** SAE 10, 20, 30, 40, 50 = 1, Petroeum = 2

4 Calcium Hydroxide & Potassium (Hydroxide=1, Sodium Hydroxide=4) 5 See Propylene Glycol 6 See Ethylene Glycol